



DOUBLE HANDLES

Enabling the fast treatment of larger areas

with minimal discomfort and no downtime

Machine Display



Exclusive And Upgraded Handle




2.1 inch




1.3 inch

Five in one , Flexible replacement of spot size



Upgraded handpiece screen

The UNT handpiece with LCD screen, can control the machine with no delay. Friendly LCD screen for handpiece, practitioners can enjoy a more intuitive, friendly work experience.



Laser Power: 600W/800W/1200W/1500W



$\phi 6\text{mm}$



15*15mm



15*20mm



15*30mm



15*40mm

UNT handpiece innovation process



| | | | |
|------------------|----------------------------|---------------------------------|--|
| Spot size | Fixed spot size | Fixed spot size | Equipped with 4 spot size |
| LCD touch screen | / | 2.4 inch (Leading design) | 2.1inch + 1.3inch (Leading design) |
| Weight | 0.4kg | 0.8kg | 0.3kg (Lighter weight) ★ |
| Laser power | 500-800W | 500-1200W | 800-1500W |
| Advantage | High quality Convenient | High quality More convenient | High quality More intelligent More economical User-friendly |

Upgraded Handpiece

φ6mm

15*15mm


15*20mm

15*30mm

15*40mm




Equipped with five sizes of spot, one UNT handpiece is suitable for whole body treatment, including larger and smaller areas. Spot size: φ6mm, 15mm*15mm, 15mm*20mm, 15mm*30mm, 15mm*40mm.



New design of optical shaping and chip self-identification. Supports chip self-identification to ensure the safety of energy output. UNT diode laser optical path, including beam shaping, collimation, focus, etc., several kinds of spot outputs with various sizes was implemented.

Exclusive Smart Android System



- 1 Function: Hair removal / Skin rejuvenation.
- 2 Gender selection: Male / Female.
- 3 Treatment of parts: Face / Arms / Chest / Abdomen / Back / Leg.
- 4 Smart cooling: L1-L5.
- 5 Treatment parameters : Smart pre-set parameters.
- 6 Advanced warning system: Intelligent detection to ensure machine safety.

Smart Android System




XPLUS5, which uses advanced Android system, is not just a machine that removes hair, but also supports Internet access, storage and intelligent information processing. Now, in the information age, smart clinics need smarter machines. Smart Clinic is a multi-faceted solution that provides a complete picture of your business; whether it is a single clinic or a chain.

Smart clinic data center

13.3-inch Android system guides you through each treatment. Intelligent selection based on the gender of the person being treated, skin color and body parts, intelligent generate accurate parameters and treatment time .

User manage

Customer management is smarter. Customer information storage and treatment records, making the treatment process more efficient.



Skin Analyzer

Magnified 75 / 200 times

Convenient operation

Supports image and video storage

Real-time viewing of
therapeutic effect




LASER THEORY

One of the first published articles describing laser hair removal was authored by the group at Massachusetts General Hospital in 1998.

It has been proven to be the safety & efficacy revolution for hair removal treatment.

People have more ways to get rid of the unwanted hair.

Blend (808nm+755nm+1064nm) lasers-The ultimate technology for dark and tanned skin. 1 SHOT=3 WAVELENGTHS, safe& effective and treatments can be performed on all patients throughout the year.



Select Skin Tone:



755nm: Especially light-colored and thin hair.

808nm: Safe for darker skin types.

1064nm: Perfect solution for darker skin types.

Treatment of parts :




One UNT handpiece is suitable for whole body treatment, including larger and smaller areas.


CLINICAL PRINCIPLE

Diode laser hair removal technology is based on the selective dynamics of light and heat. Laser beam penetrates deep into skin dermis and reach the root of hair follicles. The laser energy is selectively absorbed by the hair follicle and converted into heat which will irreversibly damage the hair follicle tissue without damaging surrounding tissue. The hair will disappear after a natural physiological process and achieve permanent hair removal effect.

Remove the unwanted hair of the body, such as hairline, lip hair, whiskers, armpit hair, body hair, bikini hair It is suitable for all skin and hair types.



PARAMENTERS



| Model Number | XPLUS5 |
|----------------------------|---|
| Wavelength | 808nm / 808nm+755nm+1064nm/808nm+755nm+1064nm+940nm |
| Laser Power | 800W, 1200W/1500W (Customizable) |
| Spot Size | φ6mm, 15mm*15mm/15mm*20mm/15mm*30mm/15mm*40mm |
| Screen Size of the Handle | 2.1 inch touch LCD screen + 1.3 inch display screen |
| Screen Size of the Machine | 15.6 inch Android screen (exclusive) |
| Energy Density | 10-120J/cm ² |
| Frequency | 1-10Hz |
| Duration | 10-300ms |
| Cooling System | Water cooling + TEC cooling + Wind cooling + Sapphire + Semiconductor |
| Refrigeration Power | > 48W |
| Energy Supply | 100-220V/50-60Hz |
| Machine Size (L*W*H) | 45cmX48cmX115cm |
| Package Size(L*W*H) | 63cm*74cm*126cm |
| Gross Weight | 90kg |
| Device Warranty | 2 year + Life-time after sale service |
| Handle Shooting Warranty | 40 millions |

COMPANY PROFILE



WAREHOUSE

Ample spare parts reserve.
Rich shell options.
Instant delivery time.



OEM/ODM

UNT has a strong research and development team, including electronics engineers (designer; AVR programming; circuit layout) construction engineer, UI designer engineer QC control engineer...etc. We provide OEM/ODM design and program update.



ABILITY

In UNT we have been at the forefront of laser diode technology since 2010, We are committed with the clinics and practices to deliver them a platform that gives them the ability to get there results that the customers demand.



Beijing UNT Technology CO.,Ltd

Address: M2-1 Area, Xinggu Development Zone, Pinggu District, Beijing 101200, China.

Website: <https://untlaser.en.alibaba.com/>

www.untlaser.com

Contact: 86-010-61960002

